



FACOM SLS.G32 - 50mm SLS Heat Shrink Sheath + D Ring

SLS.G32

DESCRIPTION

FACOM SLS.G32 - SLS Heat Shrink Sheath + D Ring

Features

Shrink tubing fitted with a strap and a metal D ring - SLS

This solution allows you to add an attachment point to all types of products and make them compatible with lanyards and carabiners from the Facom SLS range

The strap surrounds the shrink tubing for strength and maximum security for all

Fabric resistant to common solvents

Sheath equipped with an adhesive which becomes liquid with the heat during the retraction of the sheath

Optimum temperature of withdrawal - between 150 and 300' depending on the thickness and diameter of the sheath

Excellent adhesion on most substrates - crude steel - chrome or phosphate - aluminium - wood - plastic

Precautions

- Clean and degrease the product that will receive the shrink tubing
- Select the correct diameter of shrink-hose according to the allocation table
- Identify a location where the sheath will not harm ergonomics
- If possible choose a location where the sheath can not escape once retracted
- Respect the maximum weight recommended
- Heat the sheath about 3cm away with a standard heat gun
- Be careful not to burn the strap
- Allow to cool for 5 minutes to obtain optimum adhesion of the glue
- Check the bond
- Check the equipment periodically